


Reactive and Calcined Aluminas for Ceramics





Thermally Reactive Aluminas for Ceramics

Properties / Method	Unit	A 16 SG			A 1000 SG ^{1,2}			A 152 SG		
		Typical	Min.	Max.	Typical	Min.	Max.	Typical	Min.	Max.
Specific Surface Area BET	[m ² /g]	8.9	7.0	11.5	7.6	6.5	11.0	4.3	3.5	4.8
Particle Size D50*	[μm]	0.46	0.30	0.65	0.5	0.4	0.7	1.2	1.1	1.4
Particle Size D90*	[%]	1.5		1.8	1.6		2.5	2.5		3.0
Wet -325 Mesh Sieve	[%]	99.6	99.4		99.6	99.2		99.8	99.4	
Chemical Composition										
Al ₂ O ₃ by difference	[%]	99.8			99.8			99.8		
Na ₂ O	[%]	0.07		0.10	0.07		0.10	0.06		0.10
Fe ₂ O ₃	[%]	0.02		0.03	0.02		0.03	0.02		0.05
SiO ₂	[%]	0.03		0.05	0.03		0.05	0.03		0.08
CaO	[%]	0.02		0.05	0.02		0.05	0.02		0.05
MgO	[%]	0.05		0.06	0.05		0.06	0.07	0.05	0.10
B ₂ O ₃	[%]	0.002		0.006	0.005		0.01	0.015		0.02
Ceramic Properties										
Green Density	[g/cm ³]	2.17	2.15	2.25	2.11			2.34	2.20	2.40
Fired Density	[g/cm ³]	3.89	3.88		3.85			3.81	3.75	
Shrinkage	[%]	17.7	17.0	18.5				15.0	13.5	16.2
Firing Temperature 1 h Soak Time	[°C]	At 1540			At 1540			At 1620		

The typical product properties are based upon the actual averages from production data. The min-max data show our standard product specification data for these products.

All data are based upon Almatis standard test methods. All test methods are available upon request.

1) Chemistry for this product is assured through process control and verification of incoming alumina chemistry. Although each finished lot is not tested the product is certified to conform to the chemistry specifications listed.

2) This product is also available in a Super Ground Dispersible (SGD) version in which the SG product has been further processed to eliminate the soft agglomerates formed during batch grinding. The SGD version should be considered if the user's process does not include high energy mixing that will break down the soft agglomerates. Elimination of these agglomerates ensures that additives can be easily homogenized into the reactive alumina. Verification of the deagglomeration is done by performing the particle size testing without sonication of the test sample.

* Laser granulometry Bettersizer S3 Almatis global standard



Reactive Aluminas for Ceramics

Properties / Method	Unit	A 15 SG			A 3500 SG ¹		
		Typical	Min.	Max.	Typical	Min.	Max.
Specific Surface Area BET	[m ² /g]	4.9	3.5	7.5	1.9		
Wet -325 Mesh Sieve	[%]	99.8	99.4		99.8	99.4	
Particle Size D10*	[μm]	0.4	0.3	0.5	0.8	0.5	1.0
Particle Size D50*	[μm]	1.8	1.2	2.2	2.8	1.6	3.0
Particle Size D90*	[μm]	6.1	4.5	7.5			
Chemical Composition							
Al ₂ O ₃ by difference	[%]	99.8			99.8		
Na ₂ O	[%]	0.07		0.10	0.07		0.10
Fe ₂ O ₃	[%]	0.02		0.03	0.02		0.035
SiO ₂	[%]	0.02		0.05	0.02		0.05
CaO	[%]	0.03		0.05	0.03		0.06
MgO	[%]	0.04		0.06	0.01		
B ₂ O ₃	[%]	0.01		0.025	0.01		0.03
Ceramic Properties							
Green Density	[g/cm ³]	2.55	2.49	2.62			
Fired Density	[g/cm ³]	3.84	3.78				
Shrinkage	[%]	13.0	12.2	13.7			
Firing Temperature 1 h Soak Time	[°C]	At 1670					

The typical product properties are based upon the actual averages from production data. The min-max data show our standard product specification data for these products.

All data are based upon Almatis standard test methods. All test methods are available upon request.

1) Chemistry for this product is assured through process control and verification of incoming alumina chemistry. Although each finished lot is not tested the product is certified to conform to the chemistry specifications listed.

* Laser granulometry Bettersizer S3 Almatis global standard



Calcined Aluminas for Ceramics

Normal and Intermediate Soda Products

Unground		A 2			A 35			CT 800		
Properties / Method	Unit	Typical	Min.	Max.	Typical	Min.	Max.	Typical	Min.	Max.
Specific Surface Area BET	[m ² /g]	0.5		0.7	0.5	0.35	0.7	0.75	0.65	0.85
LOI 300 to 1100°C	[%]	0.2								
Green Density	[g/cm ³]				2.27			2.28	2.22	2.34
+100 Mesh** / 0.150 mm	[%]	5			5			5		
+200 Mesh** / 0.075 mm	[%]	60			60			60		
+325 Mesh** / 0.045 mm	[%]	85			85			85		
Chemical Composition										
Al ₂ O ₃ by difference	[%]	99.6			99.7			99.7		
Na ₂ O	[%]	0.25		0.35	0.13		0.18	0.11		0.15
Fe ₂ O ₃	[%]	0.02		0.035	0.02		0.035	0.02		0.04
SiO ₂	[%]	0.02		0.03	0.01		0.03	0.01		0.03
CaO	[%]	0.03		0.06	0.03		0.06	0.03		0.06
B ₂ O ₃	[%]	0.015		0.035	0.003		0.03	0.003		0.03
		A 2 -325 CR			A 35 -325 CR			CT 800 SG		
Properties / Method	Unit	Typical	Min.	Max.	Typical	Min.	Max.	Typical	Min.	Max.
Specific Surface Area BET	[m ² /g]	0.7		1.1	0.8		1.1	1.00	0.80	1.50
Particle Size D50*	[μm]	5.2	4.1	6.3	5.1			3.4	2.5	4.0
Wet -325 Mesh Sieve	[%]	99.3	99.0		99.3	99.0				
Particle Size >20μm*	[%]							1.2		3.0
Fe ₂ O ₃	[%]	0.02		0.04	0.02		0.04			
SiO ₂	[%]	0.03		0.10	0.02		0.04	0.02		0.04

The typical product properties are based upon the actual averages from production data. The min-max data show our standard product specification data for these products.

Chemistry for these products is assured through process control and verification of incoming alumina chemistry. Although each finished lot is not tested the product is certified to conform to the chemistry specifications listed.

All data are based upon Almatis standard test methods. All test methods are available upon request.

* Laser granulometry Betsizer S3 Almatis global standard

** Tyler Mesh

Calcined Aluminas for Ceramics

Low Soda Products

Properties / Method	Unit	A 3500			A 10			CL 3000			A 14		
		Typical	Min.	Max.	Typical	Min.	Max.	Typical	Min.	Max.	Typical	Min.	Max.
Specific Surface Area BET	[m ² /g]	0.5	0.35	0.60	0.2			0.7	0.60	0.75	0.55	0.45	0.70
[Primary Crystal Size D50*]**	[μm]	2.5	2.3	3.2	4.5	3.5	5.5	1.9	1.6	2.4	1.9	1.6	2.4
Green Density**	[g/cm ³]	2.27						2.27	2.24	2.32	2.31		
Chemical Composition													
Al ₂ O ₃ by difference	[%]	99.8			99.7			99.8			99.8		
Na ₂ O	[%]	0.08		0.10	0.08		0.13	0.04		0.08	0.03		0.05
Fe ₂ O ₃	[%]	0.02		0.035	0.02		0.05	0.02		0.04	0.01		0.05
SiO ₂	[%]	0.01		0.03	0.04		0.12	0.02		0.04	0.02		0.05
CaO	[%]	0.02		0.06	0.03			0.03		0.06	0.03		0.06
B ₂ O ₃	[%]	0.002		0.03	0.10		0.22	0.02		0.05	0.03		0.06
Chemical Composition													
Properties / Method	Unit	A 10 -325 ¹			A 14 -325								
		Typical	Min.	Max.	Typical	Min.	Max.	Typical	Min.	Max.	Typical	Min.	Max.
Specific Surface Area BET	[m ² /g]				0.5						0.8	0.6	1.1
Particle Size D50*	[μm]				7.9	6.5	9.7				4.9	3.5	6.1
Wet -325 Mesh Sieve	[%]				98.5	95.0					98.7	95.0	
Chemical Composition													
Al ₂ O ₃ by difference	[%]				99.7						99.8		
Na ₂ O	[%]				0.08		0.13				0.04		0.05
Fe ₂ O ₃	[%]				0.02		0.07				0.01		0.04
SiO ₂	[%]				0.04		0.14				0.03		0.08
B ₂ O ₃	[%]				0.08		0.22				0.03		0.06

The typical product properties are based upon the actual averages from production data. The min-max data show our standard product specification data for these products.

All data are based upon Almatís standard test methods. All test methods are available upon request.

1) Chemistry for this product is assured through process control and verification of incoming alumina chemistry. Although each finished lot is not tested the product is certified to conform to the chemistry specifications listed.

* Laser granulometry Bettersizer S3 Almatís global standard

** After lab grind

Standard Packaging

- 50 lb paper bags — 70 per pallet
- 25 kg paper bags — 40 per pallet
- 2500 lb super sacks — 1 per pallet
- 1 mt super sacks — 1 per pallet
- Other options are available with upcharge

Contact for sales, technical information and application assistance

Head Office
Almatís GmbH
Lyoner Straße 9
60528 Frankfurt/Germany

info@almatís.com
www.almatís.com

SDS 387